

[Supporting Software]

NovaLCT V5.4.2 or later

[New Features]

1. Added settings for input source frame rates of 96 Hz/144 Hz in the LCD menu.
2. Introduced a new dehumidification feature.

[Improvements]

1. Enhanced optical port compatibility to support the Eoptolink optical modules.
2. Added an optical enhancement mode in the LCD to improve transmission quality.

[Changes]

N/A

[Bug Fixes]

1. Fixed the issue with abnormal mapping when cascading sending cards.
2. Fixed issues related to the sending card configuration files.
3. Fixed the issue where the test pattern became unresponsive after exiting calibration when there was no active source.
4. Adjusted the test pattern on Ethernet ports to use TestVs instead of source Vs for active sources.

[Notes]

N/A